



by Schneider Electric



Main

Range of product	Harmony 9001K
Product or component type	Illuminated push-button
Device short name	K
Type of operator	Spring return
Operator profile	White flush
Operator additional information	Extended metallic guard

Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Direct
[Us] rated supply voltage	24...28 V AC/DC
Contacts type and composition	1 NO
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A (AC-15) 10 A (DC-13)
Contact operation	Standard
Device presentation	Complete product

Environment

Product certifications	UL listed file E42259 CCN NKCR NEMA CSA LR 25490 class 3211 03 CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**