

Product data sheet

Characteristics

9001K3L35YH13

PUSH BUTTON 600VAC 10A 30MM T-K



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 198.00 USD



Main

| | |
|---------------------------------|-------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Illuminated push-button |
| Device short name | K |
| Type of operator | Spring return |
| Operator profile | Yellow flush |
| Operator additional information | Extended metallic guard |

Complementary

| | |
|--------------------------------|------------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Light source | Incandescent |
| Bulb base | BA 9s |
| Light block supply | Direct |
| [Us] rated supply voltage | 24...28 V AC/DC |
| Contacts type and composition | 1 C/O |
| Connections - terminals | Screw clamp terminals |
| Operating position | Any position |
| [Ie] rated operational current | 10 A (AC-15) 10 A (DC-13) |
| Contact operation | Standard |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|--|
| Product certifications | CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR NEMA CE |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

| | |
|-----------------------|-----------------------|
| Product Life Status : | Commercialised |
|-----------------------|-----------------------|