



by Schneider Electric



### Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	K
Type of operator	Maintained
Operator profile	Gloved hand knob

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Operator position information	3 positions
Connections - terminals	Screw-clamp terminals 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1
Device presentation	Complete product

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.