

Product data sheet

Characteristics

9001K43J35LYFA

illuminated selector switch Ø 30 - amber - 3
position - stay put - 24 V AC/DC

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 167.00 USD



Main

| | |
|---------------------------|-----------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Illuminated selector switch |
| Device short name | 9001K |
| Type of operator | Stay put |
| Operator profile | Long handle red |

Complementary

| | |
|-------------------------------|----------------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Product weight | 0.54 lb(US) (0.245 kg) |
| Shape of signaling unit head | Octagonal |
| Operator position information | 3 positions |
| Contacts type and composition | Without contact block |
| Mechanical durability | 500000 cycles |
| Light block supply | Direct |
| Light source | LED |
| Bulb base | BA 9s |
| Light block colour | Amber |
| [Us] rated supply voltage | 24 V AC/DC |
| Product compatibility | 9001KA1, mounting on side 1 or 2 |
| Device presentation | Basic element |
| Compatibility code | 9001K |

Environment

| | |
|---------------------------------------|----------------------------------|
| Protective treatment | TC |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP66 conforming to IEC 60529 |

| | |
|---------------------------|--|
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 |
| Standards | UL 508 JIS C 4520 JIS C 852 CSA C22.2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 |
| Product certifications | NEMA UL 508 |
| Vibration resistance | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 003389118042957 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.55000000000000004 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|--|
| RoHS (date code: YYWW) | Compliant - since 0921 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**