


Product availability: Stock - Normally stocked in distribution facility

Price*: 66.00 USD



Main

Range of product	Harmony 9001K
Product or component type	Push-button
Device short name	K
Type of operator	Spring return
Operator profile	Orange projecting Black projecting Red projecting Green projecting Yellow projecting Blue projecting 7 colours choice flush
Operator additional information	Full guard in plastic

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 In (30 mm)
Light source	Without
Light source	Without
Light block supply	Without supply
Contacts type and composition	1 NC
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

Environment

Product certifications	CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR CE NEMA
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901033424
Package weight(Lbs)	0.29 Lb(US) (0.13 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**