



### Main

Range of product	Harmony 9001K
Product or component type	Mushroom head push-button
Device short name	K
Type of operator	Spring return
Operator profile	Green mushroom Ø 57 mm
Operator additional information	Screw-in with set screw security


### Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Light source	Without
Light source	Without
Light block supply	Without supply
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A (AC-15) 10 A (DC-13)
Contact operation	Standard
Device presentation	Complete product

### Environment

Product certifications	CE NEMA CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**