

# Product data sheet

## Characteristics

# 9001KR9P58G21

## PUSHBUTTON 600VAC 10AMP 30MM K + OPTIONS



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 215.00 USD



### Main

Range of product	Harmony 9001K
Product or component type	Push-button
Device short name	K
Operator additional information	Full guard in plastic

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 In (30 mm)
Light source	Without
Light block supply	Without supply
Contacts type and composition	Without contact block
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Basic element

### Environment

Product certifications	UL listed file E42259 CCN NKCR CE NEMA CSA LR 25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 Lb(US) (0.23 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	11.43 In (29.032 cm)
Package 1 width	4.50 In (11.430 cm)
Package 1 Length	29.03 In (73.742 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**