

# Product data sheet

## Characteristics

# 9001KS11FBH4

## SELECTOR SWITCH 600VAC 10A 30MM T-K



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 246.00 USD



### Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	K
Type of operator	Maintained
Operator profile	Black gloved hand knob

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 In (30 mm)
Operator position information	2 positions
Contacts type and composition	4 NO + 4 NC
Connections - terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1
Device presentation	Complete product

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

### Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901852612
Package weight(Lbs)	0.5 Lb(US) (0.23 kg)
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**