



Main

| | |
|---------------------------|---------------------|
| Range of product | Harmony 9001K |
| Product or component type | Selector switch |
| Device short name | K |
| Type of operator | Maintained |
| Operator profile | Black standard knob |

Complementary

| | |
|-------------------------------|--|
| Bezel material | Chromium plated metal |
| Mounting diameter | 30 mm |
| Operator position information | 2 positions |
| Connections - terminals | Screw-clamp terminals 1 x 0.22...2 x 1.5 mm ² IEC 60947-1 |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|---|
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |
| Product certifications | UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |

Product Life Status : **Commercialised**