



by Schneider Electric



Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	K
Type of operator	Maintained
Operator profile	Black standard knob

Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Operator position information	3 positions
Contacts type and composition	2 NO + 2 NC
Connections - terminals	Screw-clamp terminals 1 x 0.22...2 x 1.5 mm ² IEC 60947-1
Device presentation	Complete product

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**