



by Schneider Electric



### Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | Harmony 9001K           |
| Product or component type | Selector switch         |
| Device short name         | K                       |
| Type of operator          | Maintained              |
| Operator profile          | Black key operated knob |

### Complementary

|                               |  |
|-------------------------------|--|
| Bezel material                | Chromium plated metal  |
| Mounting diameter             | 30 mm  |
| Operator position information | 3 positions  |
| Contacts type and composition | 2 NO + 2 NC  |
| Connections - terminals       | Screw-clamp terminals 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1 |
| Device presentation           | Complete product   |

### Environment

|                           |   |
|---------------------------|---|
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13   |
| Product certifications    | CE<br>UL listed file E42259 CCN NKCR<br>CSA LR24590 class 3211 03 |

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.