



by Schneider Electric



### Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Mounting diameter	30 mm

### Complementary

Cap/operator or lens colour	Black
Contacts type and composition	Without contact block
Key number	E10
Key withdrawal position	Center Right
Operator position information	3 positions
Operator profile	Key operated knob
Operator profile	1 projecting push-button
Type of operator	Maintained

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.