

# Product data sheet

## Characteristics

# 9001KS88BH24

## SELECTOR SWITCH 600VAC 10A 30MM T-K



by Schneider Electric

Price\*: 129.00 USD



### Commercial status

This Product is Obsolete : OCT 11, 2019

This Product is Obsolete

### Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	K
Type of operator	Maintained
Operator profile	Black standard knob

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 In (30 mm)
Operator position information	4 positions
Contacts type and composition	2 NO + 1 NC
Connections - terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1
Device presentation	Complete product

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Package weight(Lbs)	8.00 Oz (226.796 g)
Returnability	No
Country of origin	MX

Contractual warranty

---

Warranty	18 months
----------	-----------

---

Product Life Status : End of commercialisation