



by Schneider Electric



Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K


Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Lens type	Domed (glass)
Cap/operator or lens colour	Red
Light block supply	Full voltage Full voltage
Shape of screw head	Round head
Operating mode	Push-to-test

Environment

Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.