



by Schneider Electric



Main

Range of product	Harmony 9001KY
Product or component type	Control station
Device short name	9001KY
Provided equipment	Label plate with STOP marking
Contact block name	KA3
Product specific application	For hoisting and mechanical handling applications
Level or class	Class II Division 2 Group G Class III

Complementary

Enclosure/cubicle description	Wall-mounted enclosure with 1 cut-out: Ø 30 mm
Enclosure material	Stainless steel
Type of installation	Indoor/Outdoor
Control station composition	1 push-button momentary with 1 NC contacts
Mechanical interlocking	Without mechanical interlock
Connector type	Screw clamp connector
Connections - terminals	Direct connection (AWG 2) solid stranded Direct connection (AWG 12) solid stranded Direct connection (AWG 24) solid stranded
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	10 A

Environment

NEMA degree of protection	NEMA 3 NEMA 4 NEMA 1 NEMA 13
Environmental characteristic	Dust and oil resistant Resistant against immersion in water
Product certifications	UL listed
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**