

Product data sheet

Characteristics

9001SK2L7R21H13

PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS



by Schneider Electric

Price*: 217.00 USD

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Bezel material	Black plastic
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Operator additional information	Without guard Screw-on plastic mushroom 2.25 in

Complementary

Line Rated Current	10 A
Cap/operator or lens colour	Red
Contact operation	Standard fingersafe
Contacts type and composition	1 NO + 1 NC
Control type	Illuminated push-button
Electrical connection	Screw clamp terminal
Light block supply	Via transformer 220 V AC 50/60 Hz Via transformer 240 V AC 50/60 Hz
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Momentary
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**