



by Schneider Electric



Main

| | |
|---------------------------|----------------|
| Range of product | Harmony 9001SK |
| Product or component type | Push-button |
| Device short name | 9001SK |

Complementary

| | |
|-----------------------|------------------|
| Bezel material | Plastic |
| Mounting diameter | 30 mm |
| Contact operation | Standard |
| Mechanical durability | 5000000 cycles |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|--|
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14 |
| IP degree of protection | IP66 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.