

Product data sheet

Characteristics

9080GK625MPO

Terminal Block Assembly, Box Lug Connector,
Natural Color, 600VAC/DC 70AMP



by Schneider Electric

Price*: 95.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Range of product	9080G
Product or component type	Terminal block
Color	Natural

Complementary

System Voltage	600 V AC/DC
[In] rated current	40 A per: CSA 70 A per: UL
Kit composition	End barrier qty: 1 End clamp(s) qty: 2 Mounting track qty: 1 Marker qty: 1 Terminal blocks qty: 25
AWG gauge	AWG 22...AWG 10 (copper)
Mounting support	9080GH track
Product certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Ambient air temperature for operation	-40...257 °F
Connections - terminals	Lug copper Tightening Torque: 11...12 lbf.in for: AWG 22...AWG 10 (copper)
Height	1.39 in
Width	1.4 in
Depth	11 in

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : End of commercialisation