

9080GR612

Terminal Block Assembly, Box Lug Connectors,
Natural Colored, 600VAC/DC 60AMP



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 46.40 USD

Main

Range of product	9080G
Product or component type	Terminal block
Product or component type	Terminal block
Color	Natural

Complementary

System Voltage	600 V AC/DC
[In] rated current	60 A per: UL 60 A per: CSA
Kit composition	End barrier qty: 1 End clamp(s) qty: 2 Terminal blocks qty: 12 Mounting track qty: 1
AWG gauge	AWG 22...AWG 8 (copper)
Mounting support	9080GH track
Product certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Protection type	Fingersafe per: DIN 57470
Ambient air temperature for operation	-40...257 °F
Connections - terminals	Lug copper Tightening Torque: 18...20 lbf.in for: AWG 22...AWG 8 (copper)
Height	1.82 in
Width	1.72 in
Depth	6 in

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	00785901958604
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**