



Main

Range of product	ZENcelo
Product or component type	Cover frame with fixing frame
Cover frame colour tint	Silver bronze

Complementary

Wiring device mounting	Flush Surface
Embedding depth	14.8 mm
Width	70 mm
Height	120 mm

Environment

Ambient air temperature for operation	-5...45 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Standards	GB 17466

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.