



Main

Range of product	ZENcelo
Product or component type	Cover frame with fixing frame
Cover frame colour tint	White

Complementary

Wiring device mounting	Surface Flush
Material	PC: surround Steel coated with zinc chromate: grid plate
Embedding depth	14.8 Mm
Width	70 Mm
Height	120 Mm

Environment

Ambient air temperature for operation	-5...45 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Standards	GB 17466

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.