



Main

Range	Acti9
Product name	Acti9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	3P

Complementary

[In] rated current	32 A 40 A 50 A 63 A 80 A 100 A 125 A
Fuse curve	GG AM
Fuse size	22 x 58 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
Locking options description	Non padlockable
9 mm pitches	12
Height	126.5 Mm
Width	105 Mm
Depth	70 Mm
Connections - terminals	Screw clamp terminals1 cable(s) 2.5...25 mm ² rigid Screw clamp terminals1 cable(s) 2.5...25 mm ² flexible
Tightening torque	3.5 N.M

Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.800 Cm
Package 1 Width	10.800 Cm
Package 1 Length	12.800 Cm
Package 1 Weight	558.000 G
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	8.500 Cm
Package 2 Width	13.200 Cm
Package 2 Length	22.600 Cm
Package 2 Weight	1.220 Kg
Unit Type of Package 3	S03
Number of Units in Package 3	18
Package 3 Height	30.000 Cm
Package 3 Width	30.000 Cm
Package 3 Length	40.000 Cm
Package 3 Weight	11.057 Kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**