



Main

Product or component type	Movement detector 300 W
Device presentation	Mechanism
Load type	230 V AC halogen lamp: 40...300 W Convactor: 40...300 W Incandescent lamp: 40...300 W
Cover plate colour tint	Aluminium
Wiring device additional information	Manual override with push-buttons NC Parallel connection : maximum 2 detectors for a load 2 wires connection

Complementary

[Ue] rated operational voltage	230 V AC 50 Hz
Product destination	OptiLine 45 installation system
Switch function	1-way
Movement detection area	9 x 18 m
Presence detection area	6 x 12 m
Detection angle	Full 180° Partial 90° left or right
Selection modes	A: automatic M: manual
Number of pin in parallel	50...300 W for 2 PIR in parallel 80...300 W for 3 PIR in parallel 100...300 W for 4 PIR in parallel 140...300 W for 5 PIR in parallel
Number of modules	2 modules
Light intensity adjustment	5...1000 Lux
Time delay	2 s...20 min
Clamping connection capacity	2 x 2.5 mm ² for flexible cable(s) 2 x 2.5 mm ² for rigid cable(s) 2 x 2.5 mm ² for solid stranded cable(s)
Wiring device mounting	Flush
Fixing mode	Clip-in
Surface finish	Satin
Mounting height	1.2...2.15 M
Height	45 Mm
Width	45 Mm
Depth	34 Mm

Environment

IP degree of protection	IP20
IK degree of protection	IK04
Ambient air temperature for operation	0...35 °C
Ambient air temperature for storage	-15...60 °C
Environmental characteristic	Ammonia Petrol Acetone Oil Liquid soap Hydrogen peroxide (H2O2) Window-cleaning fluid UV resistant Alcohol Bleach
Environmental health and issues	Halogen free
Standards	EN 60669-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**