



Main

Product or component type	Movement detector 8 A
Device presentation	Mechanism
Load type	Low voltage halogen lamp with wire-wound transformer: 1050 VA Low voltage halogen lamp with electronic transformer: 1150 VA Contactor: 200 VA Fan: 200 VA Fluorescent lamp: 2000 VA 230 V AC halogen lamp: 2000 W Convactor: 2300 W Incandescent lamp: 2300 W Compact fluorescent lamp: 500 VA
Cover plate colour tint	Aluminium
Wiring device additional information	Manual override with 5 NO push-buttons maximum 3 wires connection

Complementary

[Ue] rated operational voltage	230 V AC 50 Hz
Product destination	OptiLine 45 installation system
Switch function	1-way
Movement detection area	9 x 18 m
Presence detection area	6 x 12 m
Detection angle	Partial 90° left or right Full 180°
Selection modes	M: manual S: slave A: automatic
Number of modules	2 modules
Light intensity adjustment	5...1000 Lux
Time delay	2 s...20 min
Clamping connection capacity	2 x 2.5 mm ² for flexible cable(s) 2 x 2.5 mm ² for rigid cable(s) 2 x 2.5 mm ² for solid stranded cable(s)
Wiring device mounting	Flush
Fixing mode	Clip-in
Surface finish	Satin
Mounting height	1.2...2.15 M
Height	45 Mm
Width	45 Mm
Depth	34 Mm

Environment

IP degree of protection	IP20
IK degree of protection	IK04
Ambient air temperature for operation	0...35 °C
Ambient air temperature for storage	-15...60 °C
Environmental characteristic	Oil Bleach Window-cleaning fluid Hydrogen peroxide (H2O2) UV resistant Ammonia Alcohol Petrol Liquid soap Acetone
Environmental health and issues	Halogen free
Standards	EN 60669-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**