



Main

Range of product	Multifix
Product name	Multifix Plus
Product or component type	Ceiling box
Device presentation	With surface cover
Provided equipment	Hook Suspension chimney Surface cover
Quantity per set	Set of 10

Complementary

Function available	Anti-rotation system
Number of gangs	1 gang
Fixing mode	By screws and claws
Material	Steel PA (polyamide) 6.6 PS (polystyrene) ABS (acrylonitrile butadiene-styrene)
Mechanical robustness	Fire resistance
Colour tint	Box: blue (RAL 5015) Plastic part: white (RAL 9010)
Cable entry	6 knock-outs
Diameter	67 Mm 50 mm
Height	71 Mm
Width	71 Mm
Depth	49 Mm

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP20
Fire resistance	850 °C
Standards	IEC 60670-1

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------