



Overview

Model Name	Rack ATS, 100-120V, 15A, 5-15P In, (10) 5-15R Out
Includes	Rack Mounting brackets , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	100V , 120V
Maximum Total Current Draw per Phase	15 A
Output Connections	(10) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	100V , 120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	12 A
Input Connections	NEMA 5-15P
Cord Length	2.44 meters
Number of Power Cords	2
Acceptable Input Voltage	100-125 VAC
Maximum Input Current per phase	15 A
Load Capacity	1440 VA

Physical

Net Weight	4.7 kg
Maximum Height	44.0 mm
Maximum Width	432.0 mm
Maximum Depth	236.0 mm
Shipping Weight	6.48 kg
Shipping Height	70.0 mm
Shipping Width	486.0 mm
Shipping Depth	343.0 mm
Color	Black

Environmental

Operating Environment	-5 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	FCC Part 15 Class A , ICES-003 , PSE , TUV-C , TUV-NURTL , VCCI Class A
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant