

Product data sheet

Characteristics

ATV61HD37M3XBN

SPEED DRIVE 50 HP 230 V ATV61 w/BacNet

Price*: 5567.00 USD

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of product	Altivar 61

Complementary

[In] rated current	144 A
Cable entry	Type 1 conduit entry not included
Communication port protocol	BACnet CANopen Modbus
Input voltage	208/240 V AC
Keypad type	LCD keypad
Motor power hp	50 hp
Motor power kW	37 kW
Network number of phases	3 phases output 1 phase input

Environment

EMC filter	Without EMC filter
IP degree of protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None

Ordering and shipping details

Category	22137 - ATV61 7.5 THRU 50 HP DRIVES
Discount Schedule	CP4C
Nbr. of units in pkg.	1
Package weight(Lbs)	129
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**