

# Product data sheet

## Characteristics

# ATV61HD75N4T1LW

## 100HP460VATV61 w/ lonworksandconduitbox

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 7952.00 USD

### Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of product	Altivar 61

### Complementary

[In] rated current	160 A
Cable entry	Type 1 conduit entry outdoor
Communication port protocol	CANopen LonWorks Modbus
Input voltage	400/480 V AC
Keypad type	LCD keypad
Motor power hp	100 hp
Motor power kW	75 kW
Network number of phases	3 phases output

### Environment

EMC filter	Class A EMC filter integrated
IP degree of protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None

### Ordering and shipping details

Category	22138 - ATV61 60 THRU 150 HP DRIVES
Discount Schedule	CP4C
Nbr. of units in pkg.	1
Package weight(Lbs)	229
Returnability	N
Country of origin	CN

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**