

Product data sheet

Characteristics

ATV61HU22M3T1BN

3HP230VATV61w/ BacNetandConduitBox

Price*: 1034.00 USD

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of product	Altivar 61

Complementary

[In] rated current	11 A 8 A 1 phase
Cable entry	Type 1 conduit entry outdoor
Communication port protocol	BACnet CANopen Modbus
Input voltage	208/240 V AC
Keypad type	LCD keypad
Motor power hp	2 hp 1 phase 3 hp
Motor power kW	1.5 kW 1 phase 2.2 kW
Network number of phases	3 phases 3 phases output 1 phase input
Output voltage	<= rated supply voltage

Environment

EMC filter	Class A EMC filter integrated
IP degree of protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None

Ordering and shipping details

Category	22136 - ATV61 1/2 THRU 5 HP DRIVES
Discount Schedule	CP4C
Nbr. of units in pkg.	1
Package weight(Lbs)	17
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**