



Main

Range of product	Mont Blanc
Product or component type	Uninterruptible power supply (UPS)
Mounting support	Wall
Topology	Line interactive

Complementary

Energy values	156 J
Type of signal	Stepped approximation to a sine wave
Input voltage	230 V AC
Output voltage	230 V
Protection type	Surge arrester
Transfer time	6 ms (typical)
Network frequency	45...65 Hz
Output frequency	50...60 Hz (+/- 1 Hz)
Power range	1000 VA (output) 600 W (output)
Electrical connection	4 outlet (output), outlet standard Schuko CEE 7 1 outlet (input), outlet standard Schuko CEE 7/P
Local signalling	LED (on battery) Alarm distinctive (low battery) Alarm continuous or intermittent tone (overload)
Cable length	1.5 m
Number of cables	1
Battery type	Lead-acid battery
Product weight	5.7 kg
Height	92.5 mm
Width	160.5 mm
Depth	305 mm

Environment

Acoustic level	< 40 dBA at 1 m
Relative humidity	0...90 % non-condensing
Operating altitude	0...2000 m
Ambient air temperature for operation	0...40 °C
Product certifications	CE

Product Life Status : **Commercialised**