



Main

Product or component type	Uninterruptible power supply (UPS)
Mounting support	Wall
Topology	Line interactive

Complementary

Energy values	156 J
Type of signal	Stepped approximation to a sine wave
Network frequency	45...65 Hz
Cable length	1.52 m
Battery type	Lead-acid battery

Environment

Operating altitude	0...1968.3 m
Ambient air temperature for operation	0...40 °C
Product certifications	CE

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.