



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Rated power in W	550 W
Rated power in VA	1100 VA
Nb of power socket outlets	2 IEC 60320 C13 4 universal receptacle
Output voltage	230 V
Input voltage	230 V
Plug standard	IEC 60320 C14 NEMA 5-15P
Cable length	1.22 M
Number of cables	1

General

Provided equipment	User manual warranty card
Additional specification	Entry level
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Black
Depth	33.6 Cm
Height	21.5 Cm
Mounting preference	No preference
Net weight	9.2 Kg
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Width	13 Cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Input voltage limits	150...280 V
Maximum input current	10 A
Switching current capacity	10 A
Input protection type	3-pole circuit breaker
Input current	10 A (1 phase)
Cos phi	0.5

Output

Maximum configurable power in W	550 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Maximum configurable power in VA	1100 VA
Transfer time	4 ms typical : 6 ms maximum

Conformance

Product certifications	CE
------------------------	----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...9144.00 M
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	6 H
Battery charger power	16 W rated
Battery power in VAH	96 VAh runtime
Battery life	2...4 Year(S)
Extended runtime	0

Communications & Management

Control panel	LED status display with load and battery bar-graphs and on line : on battery : replace battery : and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm

Surge Protection and Filtering

Surge energy rate	273 J
-------------------	-------

Packing Units

Package 1 Weight	10.6 Kg
Package 1 Height	29.5 Cm
Package 1 width	24.5 Cm
Package 1 Length	44 Cm
SCC14	10731304315169

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **End of commerc. announced**

BX1100LI-MS may be replaced by any of the following products:



BVX1200LI-MS

APC Easy UPS BVX 1200VA, 230V, AVR, Universal Sockets

Qty 1

Substitution date: | Substitution