

# CH362DSWC

## 60A 3P Type4/4X 600V Heavy Duty Fusible Safety Switch, Window, Crouse-Hinds



Product availability: Stock - Normally stocked in distribution facility


### Main

Range of product	Square D
Product or component type	Receptacle Switch
Product destination	Wiring connection APJ6485 Crouse-Hinds Arktite
Line Rated Current	60 A
NEMA degree of protection	NEMA 3/3R/4/4X/5/12 stainless steel 304
Motor power hp	50 hp 600 V AC 30 hp 480 V AC
Disconnecter device type	Fusible disconnect
Short-circuit current	10 kA <= 200 kA
Device mounting	Surface
Number of poles	3
Phase	3 phases
Electrical connection	Receptacle
Product certifications	CSA
System Voltage	600 V AC/DC
AWG gauge	AWG 12...AWG 2 (aluminium) AWG 14...AWG 2 (copper)
Wiring configuration	4-wire

### Ordering and shipping details

Category	00153 - C,CH&CHU CANADA SW NON-NEG
Discount Schedule	DE1
GTIN	00785901344490
Nbr. of units in pkg.	1
Package weight(Lbs)	28.830000000000002
Returnability	Y
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Product Life Status : **Commercialised**