



Main

Range	Stago
Product or component type	Cover
Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating angle	90 °
Direction change type	Vertical
Product destination	Rising piece KG281 for cable tray 35 mm 120 mm width Rising piece KG281 for cable tray 60 mm 120 mm width Rising piece KG281 for cable tray 85 mm 120 mm width Rising piece KG281 for cable tray 110 mm 120 mm width
Fixing mode	Screwless
Material	Steel pre-galvanized
Atmospheric-corrosivity category	C2
Length	219 Mm
Height	283 Mm
Width	125 Mm
Net weight	0 Kg / set of 1

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.