



### Main

Range	Stago
Product or component type	Cover
Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

### Complementary

Operating angle	90 °
Direction change type	Vertical
Product destination	Rising piece KG281 for cable tray 35 mm 200 mm width Rising piece KG281 for cable tray 60 mm 200 mm width Rising piece KG281 for cable tray 85 mm 200 mm width Rising piece KG281 for cable tray 110 mm 200 mm width
Fixing mode	Screwless
Material	Steel pre-galvanized
Atmospheric-corrosivity category	C2
Length	219 Mm
Height	283 Mm
Width	205 Mm
Net weight	0.807 Kg / set of 1

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**