



Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 Mm
Adjustment	Fixed
Shape	Bended
Product destination	Cable tray KG281 H= 60 mm W= 120 mm
Fixing mode	By screw
Material	Steel pre-galvanized, RAL 9016
Atmospheric-corrosivity category	C2
Thickness	1 Mm
Net weight	1.018 Kg

Environment

Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages
------------------------------	-------------------------------------------------------------------------------------------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Product Life Status : **Commercialised**