



### Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management

### Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 Mm
Adjustment	Fixed
Shape	Bended
Product destination	Cable tray KG281 H= 60 mm W= 330 mm
Fixing mode	By screw
Material	Steel pre-galvanized
Atmospheric-corrosivity category	C2
Thickness	1 Mm
Height	283 Mm
Width	333 Mm
Depth	283 Mm
Net weight	1.748 Kg / set of 1

### Environment

Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages
------------------------------	---

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information

 Yes

China RoHS Regulation

 China RoHS Declaration

Product Life Status : **Commercialised**