

Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management




Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 Mm
Adjustment	Fixed
Shape	Bended
Product destination	Cable tray TV184 H= 60 mm W= 200 mm
Fixing mode	By screw
Material	Steel hot-dip galvanized
Atmospheric-corrosivity category	C3/C4
Thickness	1 Mm
Height	110 Mm
Width	200 Mm
Depth	270 Mm
Net weight	0.77 Kg / set of 1

Environment

Environmental characteristic	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
------------------------------	--

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**