



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range of product	Stago
Range	Stago
Product or component type	Bend
Device application	Cable management



Complementary

Operating angle	90 °
Direction change type	Horizontal
Inner radius	100 Mm
Adjustment	Foldable
Product destination	Cable tray KG281 H= 60 mm W= 120 mm
Fixing mode	Screwless
Shape	Bended
Material	Stainless steel pre-galvanized, RAL 1013
Atmospheric-corrosivity category	C2
Thickness	1 Mm
Height	10 Mm
Width	430 Mm
Depth	259 Mm
Net weight	0.341 Kg / set of 1

Environment

Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages
------------------------------	---

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information

 Yes

China RoHS Regulation

 China RoHS Declaration

Product Life Status : **End of commerc. - Block**