



### Main

Range of product	Stago
Product or component type	Cable ladder
Device short name	LB4000
Cable support type	High side
Environmental characteristic	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages

### Complementary

Type of side joist	Open profile
Type of rung	Perforated profile
Fixation rung	Welded
Rung dual spacing	100 mm
Fixing mode	By screw
Material	Steel, pre-galvanized
Atmospheric-corrosivity category	C2
Thickness	1 mm
Perforation location	Side perforation
Height	60 mm
Width	400 mm
Length	3000 mm
Product weight	3.64 kg / 100 m

### Environment

Standards	DIN 4102-12
-----------	-------------

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**