

Product data sheet

Characteristics

CSU76604034

Stago - ES114 tray closed 60x400mm L=3m
1mm stainless steel AISI 304



Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Unperforated
Environmental characteristic	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards

Complementary

Product destination	ES114 cable tray
Fixing mode	By screw
Material	Stainless steel AISI 304
Atmospheric-corrosivity category	C5-I
Thickness	1 Mm
Nominal cross section	24000 Mm ²
Height	60 Mm
Width	400 Mm
Length	3000 Mm
Net weight	4.17 Kg / 100 m

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Product Life Status : Commercialised

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.