

Product data sheet

Characteristics

CSU76624030

Stago - horizontal bend 90° formed 60x400mm stainless steel AISI 304

Main

Range of product	Stago
Product or component type	Bend

Complementary

Operating angle	90 °
Direction change type	Horizontal
Inner radius	100 Mm
Adjustment	Fixed
Product destination	Cable tray ES114 H= 60 mm W= 400 mm
Fixing mode	By screw
Material	Stainless steel AISI 304
Atmospheric-corrosivity category	C5-I
Net weight	3.64 Kg

Environment

Environmental characteristic	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
------------------------------	---

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.