



Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 Mm
Adjustment	Fixed
Shape	Bended
Product destination	Cable tray ES114 H= 60 mm W= 150 mm
Fixing mode	By screw
Material	Stainless steel AISI 304
Atmospheric-corrosivity category	C5-I
Thickness	1 Mm
Height	236 Mm
Width	153 Mm
Depth	236 Mm
Net weight	1.3 Kg / set of 1

Environment

Environmental characteristic	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
------------------------------	---

Product Life Status : **Commercialised**