



### Main

Range	Digilink
Product or component type	Patch cord
Cable shielding type	UTP
Colour tint	Yellow

### Complementary

Type of cable	4 twisted-pairs cable
Communication network category	6
Connector type	RJ45
Material	PC (polycarbonate) plug
AWG gauge	AWG 23 stranded cable
Insulation resistance	$\geq 500$ mOhm @ 500 V DC
Contacts material	Gold over nickel
[In] rated current	$\leq 1.5$ A
Contact resistance	$\leq 20$ mOhm
[Ue] rated operational voltage	$< 72$ V DC
Cable length	5 m

### Environment

Flame retardance	UL 94 V-0
Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 class E
Product certifications	UL/ETL verified UL listed

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------