



Main

Range	Digilink
Product or component type	Patch cord
Cable shielding type	UTP
Colour tint	Blue

Complementary

Type of cable	4 twisted-pairs cable
Communication network category	5e
Connector type	RJ45
Material	PC (polycarbonate) plug
AWG gauge	AWG 24 stranded cable
Insulation resistance	≥ 500 mOhm @ 500 V DC
Contacts material	Gold over nickel
[In] rated current	≤ 1.5 A
Contact resistance	≤ 20 mOhm
[Ue] rated operational voltage	< 72 V DC
Cable length	1 m

Environment

Flame retardance	UL 94 V-0
Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 class D
Product certifications	UL/ETL verified UL listed

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------