



Main

Product or component type	Multi-mode adaptor
---------------------------	--------------------

Complementary

Connector type	SC
Exchange mode	Duplex
Insertion loss	< 0.3 dB
Number of matings	1000 cycles
Product compatibility	For 50/125 and 62.5/125 µm optical fibre
Contacts material	Phosphor bronze

Environment

Ambient air temperature for operation	-40...80 °C
Product certifications	UL listed
Standards	ISO/IEC 11081 EIA/TIA-568-C.0 IEC 874

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1801 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**