



Main

Range	Neo C-Metro
Product or component type	Dimmer
Bulb type	LED, blue
Number of gangs	1 gang
Colour tint	Grey silver

Complementary

Wiring device mounting	Surface Flush
Power range	40...600 VA incandescent lamp 40...600 VA low voltage halogen lamp with electronic transformer
[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	1 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for stranded cable(s) 1 x 2.5 mm ² for solid cable(s) 1 x 2.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) 2 x 2.5 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 Mm
Height	87 Mm
Depth	26 Mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 16915.2 IEC 60669-2-1

Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------