



Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	1-way
Switch application	Switch
Bulb type	Fluorescent (green)
Colour tint	Grey silver


Complementary

Rated current	100 mA at 24 V DC
Number of gangs	1 gang vertical
Material	Brass: terminals Polycarbonate: plastic part
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 Mm
Height	87 Mm
Embedding depth	23 Mm
Depth	36 Mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. announced**