

# Product data sheet

## Characteristics

# E3032DMLV\_EAGS

Neo ELV+ - courtesy panel - do not disturb/  
make up room - grey silver



### Main

Range of product	Neo ELV+
Product or component type	Courtesy panel
Device application	Control
Number of channels	2
Additional information	5 or 12 V DC selectable
Colour	Silver

### Complementary

Connector type	RJ45 5e)
Output type	Voltage free dry contact
Rated current	20 mA at < 24 V DC
Status LED	LED amber do not disturb LED amber make up room
Number of gangs	2 gangs horizontal
Width	87 Mm
Height	87 Mm
Embedding depth	20.3 Mm
Depth	35 Mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %

### Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
-------------------	--

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.