



### Main

Product or component type	Power socket-outlet
Switch function	Switch
Rated current	15 A, 250 V, , AC, 50 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	Red

### Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate with grid plate Polycarbonate with surround
Clamping connection capacity	2 x 2.5 mm <sup>2</sup> for solid cable(s)
Width	87 mm
Height	87 mm
Depth	31.8 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 546 MS 1577 SS 472

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**